

Analytical Mill Tube Mill control IKA

[Product in eShop](#)

[Home](#) / [Assortment](#) / [Laboratory consumables & instruments](#) / [Sample Handling](#) / [Milling](#) / [Mills](#) / [Analytical Mill Tube Mill control IKA](#)

Product Data

- Clearly arranged, multilingual OLED-display
- Timer, adjustable from 5 s to 3 min
- USB interface for control and documentation of all the parameters
- Interval operation available
- Infinitely variable speed from 5000 to 25000 rpm
- Various operating modes
- Adjustable safety speed
- Adjustable safety time
- Programmable and storable test conditions
- Error Code Display
- Reproducible test results
- Easy operation with touch keypad
- Dust proof sealed housing
- Quiet operation

Technical Data

- Usable volume max.: 40 ml
- Material beater/cutter: stainless steel 1.4034
- Dimensions (W x H x D) 180 x 170 x 300 mm
- Protection class according to DIN EN 60529: IP 30

| Item No. | type no. | speed | Price |
|------------|-------------------|--------------------|--------------|
| 17.2901.00 | Tube Mill Control | 5000 - 25000 U/min | CHF 2'749.00 |

Accessories

| Item No. | Description | Price |
|------------|--|-----------------|
| 17.2901.10 | Grinding chamber for IKA Tube Mill control | from CHF 108.00 |

* The prices are non-binding and are to be understood as selling prices in Swiss francs without value added tax (VAT), as well as all other fees, charges and taxes. The prices displayed in the eShop may differ from the PDF file due to regular updates.

** Please note that when ordering chemicals and detergents, transport and packaging costs for hazardous goods as well as legally prescribed fees are charged. These will be shown in detail on the order confirmation, which you will receive in addition to the confirmation of receipt.

*** Further information such as technical information and safety data sheets can be found online in our eShop.

**** The PDF file was created on www.huberlab.ch on 05.06.2024 at 12:30 oclock.

www.huberlab.ch