

PP pump hose/stopcock 50cm



Product in eShop



[Home](#) / [Assortment](#) / [Laboratory consumables & instruments](#) / [Liquid Handling](#) / [Pump](#) / [Drum pumps](#) /

Product Data

Fasspumpen aus Polypropylen ermöglichen ein schnelles Abfüllen von Flüssigkeiten aus Fässern, Kanistern und Tanks. Durch die gute chemische Beständigkeit von PP können auch Säuren, Laugen und aggressive Reiniger abgefüllt werden.

- Dichtungen aus PTFE
- Tauchrohr Ø 32 mm
- Förderleistung bis ca. 12 l/min
- Für Fässer und Tanks von 60 – 1000 Liter

Item No.	immersion depth	total length	stroke	Price
15.5600.20	500 mm	600 mm	200 ml	CHF 223.35
15.5600.21	650 mm	740 mm	230 ml	CHF 223.35
15.5600.22	800 mm	895 mm	260 ml	CHF 231.00
15.5600.23	1000 mm	1090 mm	300 ml	CHF 243.00

Accessories

Item No.	Description	Price
15.5600.13		from CHF 36.90

More product images



* The prices are non-binding and are to be understood as selling prices in Swiss francs without value added tax (VAT), as well as all other fees, charges and taxes. The prices displayed in the eShop may differ from the PDF file due to regular updates.

** Please note that when ordering chemicals and detergents, transport and packaging costs for hazardous goods as well as legally prescribed fees are charged. These will be shown in detail on the order confirmation, which you will receive in addition to the confirmation of receipt.

*** Further information such as technical information and safety data sheets can be found online in our eShop.

**** The PDF file was created on www.huberlab.ch on 17.05.2024 at 20:27 oclock.

www.huberlab.ch